



FMS-2000 Critical Environment Controller



Sleek new casing and user interface This low profile device clearly displays the information that's most important to you - and is legible from across the room.

Connect into Metasys® or any BAS to track important data and use trends to create a more energy efficient facility.

Incorporating user feedback The design team worked directly with end users to ensure that the interface is configurable to meet the needs of various users from facility managers to researchers and operating room nurses.

The patented Safety Halo™ edge lighting is great for long corridors and it cuts down on audible alarm fatigue. You can also schedule the light to dim for evening setbacks.

Door switch connections reduce nuisance alarms during the quick moments of doors opening and closing.

Maintenance-free pressure sensor Our zero drift embedded pressure sensors provide highly accurate maintenance-free sensing.

Feature rich The user can customize what they want to see on the home screen - easily track and verify your temperature, pressure, humidity, and air changes.

